


9 Antenna types

Several antenna types can be delivered with the Televend box set. Ensure good connectivity by selecting the right antenna. Usually, it is preferred that Televend reports a GSM signal strength of 20% or more for stable operation. Bluetooth antenna used depends on your preference and usage.

Part nr.	Usage	Gain	Mounting/Usage	Image
AN01	GSM	2,1 dBi	Internal, screw	
AN02	GSM	2,1 dBi	Internal, adhesive, install on a front-facing plastic surface, for areas with good signal strength	
AN03	GSM	5,0 dBi	External, magnetic, install on top of the machine, for areas with bad signal strength	
AN03S	GSM	2,2 dBi	External, magnetic, install on top of the machine, for areas with lower signal strength	
AN04	GSM	2,2 dBi	External, screw-on top machine's casing, for areas with lower strength, vandal-proof.	
AN01-BT	Bluetooth	2,1 dBi	Internal, screw	
AN05-BT	Bluetooth	2,1 dBi	The external, best visibility, machine's front-facing mount, recommended for the Televend wallet, vandal-proof.	